

USB PLUG A	BRAID+DRAIN	USB FEMALE A
PIN 1	RED	PIN 1
PIN 2	WHITE	PIN 2
PIN 3	GREEN	PIN 3
PIN 4	BLACK	PIN 4

MATERIAL LIST:

④	OUTER MOLD	PVC COLOUR FOR TRANSPARENT	2	
③	USB A TYPE	USB A /F SOLDER TYPE, WHITE PBT INSULATION, THE PIN GOLD PLATING, THE SHELL FOR NICKEL PLATING	1	
②	USB A TYPE	USB A /M SOLDER TYPE, WHITE PBT INSULATION, THE PIN GOLD PLATING, THE SHELL FOR NICKEL PLATING	1	
①	CABLE	USB 2.0 28AWG(7/0.12BO)*1P+28AWG(7/0.12BO)*2C)+AL-F0IL+DRAIN(7/0.12 TC)+BRAID(16/3/0.12 AL-M0)+PVC/TRANSPARENT JACKET OD:4.0±0.2MM	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QTY	REMARK

NOTE:

1. Electrical test:
 - (1). 100% open short & miss wire test;
 - (2). Insulation resistance: DC 300V 10MΩ;
 - (3). Contactor resistance: 3Ω Max;
 - (4). Dielectric strength: 100V AC/Minute, 1mA.
2. PRINT WORD: AWM STYLE 2725 80°C 30V VW-1 28AWG×1P 28AWG×2C
 3. PACKING: 1PCS/PE BAG
 4. ROHS AND REACH COMPLIANT


UNO ELECTRONIC LIMITED (HK)

TEL: 0086-574-87990380; FAX: 0086-574-87990385

CUSTOMER	CEI Conrad Electronic Int. (HK) Ltd	ITEM NO.	SEE THE CHART
PRODUCT NAME	USB 2.0 AM/AF	UNIT	MM

BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.	DRAWNBY	CHECKBY	APPROBY	DATE
		NEW	2013.12.18	A	FERGUS	ALVAN		2013.12.18

ITEM NO.	LENGTH	Weight
	500+60/-0	
	1000+60/-0	
971747	1800+100/-0	54.5G
972303	3000+100/-0	78.5G
972024	4500+100/-0	108.5G



UNO ELECTRONIC LIMITED (HK)

TEL : 0086-574-87990380 ; FAX : 0086-574-87990385

CUSTOMER CEI Conrad Electronic Int. (HK) Ltd ITEM NO. SEE THE CHART

PRODUCT NAME USB 2.0 AM/AF UNO ITEM NO. UNIT MM

DRAWNBY CHECKBY APPROBY DATE

FERGUS ALVAN 2013. 12. 18

BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.
		NEW	2013. 12. 18	A