

	Article description			Article-no./ GTIN	garantee
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	Mud-dry vacuum cleaner TSS 1600 K			30519	24 month
	Articel Information				
	Produkt dimensions in cm			Weight (kg) gross	
	Width	Depth	Height		
	51.0	39.5	58.8	7.6	
	Packaging dimensions in cm			Weight (kg) net	
	Width	Depth	Height		
35.0	35.2	55.1	8.8		
Masterbox Informationen					
Packaging dimensions in cm			Weight (kg)	Qty.	
Width	Depth	Height	gross		
-	-	-	-	-	

Mud-dry vacuum cleaner TSS 1600 K

Description:

The 1,600 watt mud and dry vacuum cleaner is a real all-rounder for cleaning and draining. This powerful device is ideal for removing mud, algae and other types of dirt from ponds, pools, basements, garages and similar areas. The practical automatic emptying system and a transparent suction pipe with flow control make work not only more effective, it also makes it easier and more controllable.

Technical Data:

Mains voltage / frequency: 1,600 Watt
 Nominal performance: 220 - 240 V~ / 50 Hz
 Power cord: 4 m / H05VV-F
 Suction height max.: 1.8 m
 Tank size: 30 l
 Suction hose: 4 m (Ø 35 mm)
 Drain hose: 1.5 m (Ø 35 mm)
 Temperature medium max.: 35 °C
 Suction power max.: 200 mbar (0.20 bar)

Scpoe of delivery:

- Suction hose 4 m
- Suction pipe 2 m
- 4-part (2 x transparent)
- Drain hose 1.5 m
- Suction nozzle
- Sponge filter
- Discharge filter bag

Approval marks:

