

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013

INFORMATION		Value	Unit
1. Supplier name or trademark		SONY	
2. Model identifier		KD-65X80J	
3. Energy Efficiency Class for Standard Dynamic Range (SDR)		G	
4. On mode power demand for Standard Dynamic Range (SDR)		130	W
5. Energy Efficiency Class for High Dynamic Range (HDR)		G	
6. On mode power demand in High Dynamic Range (HDR) mode		193	W
7. Off mode, power demand		n.a.	W
8. Standby mode power demand		0,5	W
9. Networked standby mode power demand		2,0	W
10. Electronic display category		Television	
11. Size ratio		16 : 9	
12. Screen resolution (pixels)		3 840 x 2 160	pixels
13. Screen diagonal		163,9	cm
14. Screen diagonal		65	inches
15. Visible screen area		11 478,1	cm ²
16. Panel technology used		LED LCD	
17. Automatic Brightness Control (ABC) available		Yes	
18. Voice recognition sensor available		No	
19. Room presence sensor available		No	
20. Image refresh frequency rate		50	Hz
21. Minimum guaranteed availability of software and firmware updates (until):		19 03 2029	
22. Minimum guaranteed availability of spare parts (until)		19 03 2028	
23. Minimum guaranteed product support (until)		19 03 2023	
24. Power supply type:		Internal	
i External standardised power supply (included in the product box)	Standard name	-	
	Input voltage	-	V
	Output voltage	-	V
ii External standardised suitable power supply (if not included in the product box)	Standard name	-	
	Required output voltage	-	V
	Required delivered current	-	A
	Required current frequency	-	Hz