

# JUMP STARTER & AIR INFLATOR

JA301

Two in One 20000mAh  
150PSI



**LOKITHOR**

# LOKITHOR



- ① LED Light
- ② LED Light Switch
- ③ Power Button
- ④ BAR/PSI Unit Switch Button
- ⑤ Display
- ⑥ The Button for Presetting Tire Pressure
- ⑦ Air Inflator Start-stop Button
- ⑧ Type-C Charge Port / USB-A Discharge Port
- ⑨ EC8 Starting Port
- ⑩ Air Inflator Output Port

## JUMP STARTER & AIR INFLATOR TWO IN ONE

### Parameter Specification:

Battery Capacity	20000mAh (74Wh)
Starting Voltage	12V
Starting Current	1000A
Peak Current	2000A
Pressure Range	10~150 psi
Sensor Accuracy	± 2psi
Input	USB-C 5V/3A, 9V/2A
Output	USB-A 5V/3A, 9V/2A
Polarity	Red(+), Black(-)
Charging Temp	0°C to 45°C
Operating Temp	-20°C to 50°C
Storage Temp	-20°C to 50°C
Battery life	>1000 cycles in good condition
Charging Time	4 to 7.5 Hours

### Main Feature:

- 1) Jump Starter  
Up to 8-Liter gasoline and 6-Liter diesel  
12 V engines
- 2) Air Inflator  
Max. 150 PSI
- 3) LED Lighting  
300 LUMENS  
3 Modes: Constant Light/Strobe/SOS
- 4) Power bank  
USB-A\*1 (QC3.0, 5V3A, 9V2A)

### Certification

FC CE RoHS

