



TECHNICAL INFORMATION

Shape:	Square
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	Matt Black
Body Type:	Aluminium Body + Clear PC Diffuser
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Rated Load:	Max 35W
Dimension:	80x80x500mm

BOLLARD LAMPS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 7564 - 1644

[View more details](#)



FEATURES

- Perfect replacement for traditional Bollard lamps
- Strong and sturdy Aluminium Body + Clear PC Diffuser body
- Compatible with GU10 holder type (Fitting only - light not included)
- Elegant Matt Black colour finish
- Suitable for gardens, patio, pathways etc.

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs): 1.05
Unit CBM: 0.004131
Dimension: 80x80x500mm

MASTER BOX PACKAGING

Box Qty: 4
Qty Per Pallet: 288
Length (Box) mm: 90
Width (Box) mm: 90
Height (Box) mm: 510

LISTING DETAILS

Commodity Code: 9405109890
Ean Code: 3800157636377