



TECHNICAL INFORMATION

Shape:	Round
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	Matt Black
Body Type:	Aluminium Body + Opal PC Diffuser
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Rated Load:	Max 35W
Dimension:	80x80x800mm

BOLLARD LAMPS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 7568 - 1644

[View more details](#)



 **GU10**

Compatible with any standard **GU10** lamp.
*Lamps are not included

**ALUMINIUM BODY
OPAL PC DIFFUSER**



IP54
RATING



3 YEAR
WARRANTY

FEATURES

- Perfect replacement for traditional Bollard lamps
- Strong and sturdy Aluminium Body + Opal PC Diffuser body
- Compatible with GU10 holder type (Fitting only - light not included)
- Elegant Matt Black colour finish
- Suitable for gardens, patio, pathways etc.

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs):	1.56
Unit CBM:	0.00648
Dimension:	80x80x800mm

MASTER BOX PACKAGING

Box Qty:	4
Qty Per Pallet:	200
Length (Box) mm:	90
Width (Box) mm:	90
Height (Box) mm:	800

LISTING DETAILS

Commodity Code:	9405109890
Ean Code:	3800157636414