



#### TECHNICAL INFORMATION

|              |                   |
|--------------|-------------------|
| Input Power: | AC:220-240V, 50Hz |
| Unit Color:  | Black             |
| Body Type:   | Aluminium+Glass   |
| Dimmable:    | No                |
| Beam Angle:  | 300°              |
| Rated Load:  | Max 60W           |
| Dimension:   | 235x225mm         |



3 YEAR  
WARRANTY



IP44  
RATING

#### FEATURES

- Traditional garden lamps designed to meet modern day requirements
- Strong and sturdy Aluminium+Glass body
- Offering IP44 Ingress protection
- Compatible with E27 holder type (Fitting only - lamp not included)
- Suitable for gardens, patio, pathways etc.

#### WALL LAMPS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 8686 - 938

[View more details](#)



COMPATIBLE WITH  
**E27 LAMPS**  
\*Bulbs are not included



#### PACKAGING

|                     |           |
|---------------------|-----------|
| Gross Weight (Kgs): | 1.1       |
| Unit CBM:           | 0.009522  |
| Dimension:          | 235x225mm |

#### MASTER BOX PACKAGING

|                  |     |
|------------------|-----|
| Box Qty:         | 10  |
| Qty Per Pallet:  | 140 |
| Length (Box) mm: | 180 |
| Width (Box) mm:  | 230 |
| Height (Box) mm: | 230 |

#### LISTING DETAILS

|                 |               |
|-----------------|---------------|
| Commodity Code: | 9405109890    |
| Ean Code:       | 3800157654913 |