



TECHNICAL INFORMATION

Input Power:	AC:220-240V, 50Hz
Unit Color:	Satin Nickel
Body Type:	Stainless Steel + PC
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Rated Load:	Max 60W
Dimension:	Ø110x800mm

BOLLARD LAMPS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 8625 - 1122

[View more details](#)



3 YEAR
WARRANTY



IP44
RATING

FEATURES

- Perfect replacement for traditional Bollard lamps
- Strong and sturdy Stainless Steel + PC body
- Compatible with E27 holder type (Fitting only - light not included)
- Elegant Satin Nickel colour finish
- Suitable for gardens, patio, pathways etc.



PACKAGING

Gross Weight (Kgs):	1
Unit CBM:	0.011664
Dimension:	Ø110x800mm

MASTER BOX PACKAGING

Box Qty:	6
Qty Per Pallet:	60
Length (Box) mm:	120
Width (Box) mm:	120
Height (Box) mm:	810

LISTING DETAILS

Commodity Code:	9405109890
Ean Code:	3800157652445