



TECHNICAL INFORMATION

Input Power:	AC:220-240V, 50Hz
Unit Color:	White+Stainless Steel
Body Type:	Stainless Steel + PC
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Rated Load:	Max 60W
Dimension:	Ø76x376mm

E27 WALL FITTINGS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 8623 - 1667

[View more details](#)



IP44
RATING
DUST &
MOISTURE PROTECTION



3 YEAR
WARRANTY



IP44
RATING

FEATURES

- Perfect replacement for traditional wall fittings
- Strong and sturdy Stainless Steel + PC body
- Compatible with E27 holder type (Fitting only - light not included)
- Elegant White+Stainless Steel colour finish
- Suitable for pathways, stairways, corridors, walkways etc.



PACKAGING

Gross Weight (Kgs):	0.47
Unit CBM:	0.0027455
Dimension:	Ø76x376mm

MASTER BOX PACKAGING

Box Qty:	12
Qty Per Pallet:	360
Length (Box) mm:	85
Width (Box) mm:	85
Height (Box) mm:	380

LISTING DETAILS

Commodity Code:	9405109890
Ean Code:	3800157652421