



TECHNICAL INFORMATION

Input Power:	AC:220-240V, 50Hz
Unit Color:	Stainless Steel
Body Type:	Stainless Steel
Operation Temperature:	-25°C to +50°C
Rated Load:	Max 35Wx2
Dimension:	110x67x220mm
Sensor Type:	PIR

GU10 UP DOWN FITTINGS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 7503 - 1256

[View more details](#)



FEATURES

- Perfect replacement for traditional wall fittings
- Designed with PIR Sensor
- Strong and sturdy Stainless Steel body
- Compatible with GU10 holder type (Fitting only - light not included)
- Elegant Stainless Steel colour finish
- Suitable for pathways, stairways, corridors, walkways etc.

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs):	0.865
Unit CBM:	0.002026875
Dimension:	110x67x220mm

MASTER BOX PACKAGING

Box Qty:	12
Qty Per Pallet:	480
Length (Box) mm:	115
Width (Box) mm:	75
Height (Box) mm:	235

LISTING DETAILS

Commodity Code:	9405109890
Ean Code:	3800157617628