

Data Sheet

Heat shrinking set of 300 pcs, 3:1, Black



Technical data

Shrink-ratio: 3:1

Material: PE

Shrinking temperature: 80 ~ +125 °C

Operating temperature: -20 ~ +130 °C

Tensile Strength: 10 Mpa

Dielectric strength: 1 kV/mm

Length: 60 mm

100 pcs x 1.6 (inner dia.) mm
70 pcs x 2.4 (inner dia.) mm
50 pcs x 3.2 (inner dia.) mm
30 pcs x 4.8 (inner dia.) mm
20 pcs x 6.4 (inner dia.) mm
10 pcs x 7.9 (inner dia.) mm
10 pcs x 9.5 (inner dia.) mm
10 pcs x 12.7 (inner dia.) mm