

1500BSF

Product no.: 1500BSF

Pneumatic side cutter and tip cutter. Requires 4 - 6 bar oil-free clean compressed air




Pneumatic cutter



Handy, light and precise



Extremely versatile thanks to a selection of different cutting heads



[source images](#)

The Perfect Cut - Strong, sharp and precise, every time

1500 Weller Erem pneumatic side cutters are light and precise. Thanks to a selection of different cutting heads they can operate extremely versatile. The cutters are suitable for cutting conventional components, soft metals or small plastic parts. The cutting heads can be interchanged easily.

THE PERFECT CUT

Strong, sharp and precise - every time

- + 1 Million Movements**
Magic Spring™ design enables maximum durability with constant spring force movements
- + Quality**
Uncompromising Swiss quality created to be strong, durable and sharp
- + Precision**
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap
- + Strong and Sharp**
Hand-crafted cutting edges for superior strength and sharpness
- + Comfort, Security and Grip**
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology
- ESD Safe**
Made from ESD-safe material to prevent damage to sensitive components

Swiss Made

weller-tools.com **Weller**
Erem





Technical Data

Length mm	130
Length of cutting edges mm	---
Head width mm	---
Head thickness mm	---
Head length mm	---
Max. cutting capability – hard wire mm	---
Weight in oz	5.644
Length of cutting edges Inches	---
Head width Inches	---
Head thickness Inches	---
Head length Inches	---
ESD-safe	on
Cut	---
Max. cutting capability – medium hardness mm	---
Max. cutting capability – copper wire mm	---
Length inches	5.118
Weight in g	160
Erem applications	Microelectronic