



1512N

Product no.: 1512N

Side cutter - oval head for 1500BSF Pneumatic-cutter




This is the standard head shape.



It is used for all cutting jobs in easy-to-reach areas.



The oval head provides for a high cutting capacity and is characterised by its robustness.



[source images](#)

The Perfect Cut - Strong, sharp and precise, every time

1500 Weller Erem pneumatic side cutters are light and precise. Thanks to a selection of different cutting heads they can operate extremely versatile. The cutters are suitable for cutting conventional components, soft metals or small plastic parts. The cutting heads can be interchanged easily.

THE PERFECT CUT

Strong, sharp and precise - every time

+ Precision
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap

+ Quality
Uncompromising Swiss quality created to be strong, durable and sharp

+ Strong and Sharp
Hand-crafted cutting edges for superior strength and sharpness

+ 1 Million Movements
Magic Spring™ design enables maximum durability with constant spring force movements

+ Comfort, Security and Grip
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology

ESD Safe
Made from ESD-safe material to prevent damage to sensitive components

Swiss Made

weller-tools.com **Weller**
Erem





Technical Data

Length mm	---
Length of cutting edges mm	10
Head width mm	11
Head thickness mm	6
Head length mm	---
Max. cutting capability – hard wire mm	---
Weight in oz	1.139
Length of cutting edges Inches	0.394
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	---
ESD-safe	on
Cut	Semi-flush
Max. cutting capability – medium hardness mm	---
Max. cutting capability – copper wire mm	Ø 1,6
Length inches	---
Weight in g	32.3
Erem applications	Microelectronic