



# 1522N

Product no.: 1522N

Side cutter - oval head for 1500BSF Pneumatic-cutter



This is the standard head shape.



It is used for all cutting jobs in easy-to-reach areas.



The oval head provides for a high cutting capacity and is characterised by its robustness.



[source images](#)

## The Perfect Cut - Strong, sharp and precise, every time

1500 Weller Erem pneumatic side cutters are light and precise. Thanks to a selection of different cutting heads they can operate extremely versatile. The cutters are suitable for cutting conventional components, soft metals or small plastic parts. The cutting heads can be interchanged easily.

## THE PERFECT CUT

Strong, sharp and precise - every time

- + 1 Million Movements**  
Magic Spring™ design enables maximum durability with constant spring force movements
- + Quality**  
Uncompromising Swiss quality created to be strong, durable and sharp
- + Precision**  
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap
- + Strong and Sharp**  
Hand-crafted cutting edges for superior strength and sharpness
- + Comfort, Security and Grip**  
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology
- ESD Safe**  
Made from ESD-safe material to prevent damage to sensitive components

Swiss Made

weller-tools.com **Weller**  
Erem





**Technical Data**

Length mm	69
Length of cutting edges mm	10
Head width mm	11
Head thickness mm	6
Head length mm	19
Max. cutting capability – hard wire mm	---
Weight in oz	1.139
Length of cutting edges Inches	0.394
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	0.748
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	---
Max. cutting capability – copper wire mm	Ø 1,6
Length inches	2.717
Weight in g	32.3
Erem applications	Microelectronic