



2476TX1

Product no.: 2476TX1

Side cutter - tapered head.



The jaws of the cutter have straight edges and taper to a point. This head shape allows access to difficult to reach areas but reduces the cutting capacity in comparison to the same size oval head cutter.



Series 2400 MagicSense model



Hard metal blades - smooth and precise rounded tips



[source images](#)

The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 2400 Magic Sense is a range of medium-sized precision cutters that combines robustness, visibility and accessibility. A large variety of head shapes for precision work in hard-to-reach areas. The optimized ergonomic shape of the Series 2400 MagicSense prevents hand fatigue. These cutters are manufactured from improved induction-hardened cutting edges up to 64 – 65 HRC for an extremely long service life. The cutting edges are made from special tool steel. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.

THE PERFECT CUT

Strong, sharp and precise - every time

- + 1 Million Movements**
Magic Spring™ design enables maximum durability with constant spring force movements
- + Quality**
Uncompromising Swiss quality created to be strong, durable and sharp
- + Precision**
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap
- + Strong and Sharp**
Hand-crafted cutting edges for superior strength and sharpness
- + Comfort, Security and Grip**
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology
- ESD Safe**
Made from ESD-safe material to prevent damage to sensitive components

Swiss Made

weller-tools.com **Weller**
Erem





Technical Data

Length mm	128
Length of cutting edges mm	10
Head width mm	11
Head thickness mm	6
Head length mm	18.5
Max. cutting capability – hard wire mm	Ø 0,4
Weight in oz	2.589
Length of cutting edges Inches	0.394
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	0.728
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 0,5
Max. cutting capability – copper wire mm	Ø 1,0
Length inches	5.039
Weight in g	73.4
Erem applications	Microelectronic