







530E10

Product no.: 530E10

Distance cutter, cuts wire to a length of 1.0 mm/.039 Inch

-  Special tool steel
-  ESD-safe
-  Fixed cutting length



[source images](#)


The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 500 Micro is a full range of medium sized, robust, precision cutters with a wide range of head shapes. The cutters are manufactured from high grade tool steel. The cutting edges are hardened to Rockwell 63-65 HRC. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.

THE PERFECT CUT

Strong, sharp and precise - every time

- + 1 Million Movements**
Magic Spring™ design enables maximum durability with constant spring force movements
- + Quality**
Uncompromising Swiss quality created to be strong, durable and sharp
- + Precision**
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap
- + Strong and Sharp**
Hand-crafted cutting edges for superior strength and sharpness
- + Comfort, Security and Grip**
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology
- + ESD Safe**
Made from ESD-safe material to prevent damage to sensitive components

 Swiss Made

weller-tools.com **Weller**
Erem





Technical Data

| | |
|--|-------|
| Length mm | 120 |
| Length of cutting edges mm | --- |
| Head width mm | --- |
| Head thickness mm | --- |
| Head length mm | --- |
| Max. cutting capability – hard wire mm | --- |
| Weight in oz | 2.469 |
| Length of cutting edges Inches | --- |
| Head width Inches | --- |
| Head thickness Inches | --- |
| Head length Inches | --- |
| ESD-safe | on |
| Cut | Flush |
| Max. cutting capability – medium hardness mm | --- |
| Max. cutting capability – copper wire mm | Ø 1,2 |
| Length inches | 4.724 |
| Weight in g | 70 |
| Erem applications | --- |