




# 530E12

Product no.: 530E12

Distance cutters cuts copper wire to a length of 1.2 mm/.047 Inch

-  Special tool steel
-  ESD-safe
-  Fixed cutting length



[source images](#)

## The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 500 Micro is a full range of medium sized, robust, precision cutters with a wide range of head shapes. The cutters are manufactured from high grade tool steel. The cutting edges are hardened to Rockwell 63-65 HRC. The precision cutters have a nonreflecting surface, are ESD safe and resharable.

## THE PERFECT CUT

Strong, sharp and precise - every time

**+ 1 Million Movements**  
Magic Spring™ design enables maximum durability with constant spring force movements


**+ Quality**  
Uncompromising Swiss quality created to be strong, durable and sharp

**+ Precision**  
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap

**+ Strong and Sharp**  
Hand-crafted cutting edges for superior strength and sharpness

**+ Comfort, Security and Grip**  
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology

**ESD Safe**  
Made from ESD-safe material to prevent damage to sensitive components

 Swiss Made

weller-tools.com **Weller**  
Erem





**Technical Data**

Length mm	120
Length of cutting edges mm	---
Head width mm	---
Head thickness mm	---
Head length mm	---
Max. cutting capability – hard wire mm	---
Weight in oz	2.469
Length of cutting edges Inches	---
Head width Inches	---
Head thickness Inches	---
Head length Inches	---
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	---
Max. cutting capability – copper wire mm	Ø 1,2
Length inches	4.724
Weight in g	70
Erem applications	---