






530E15A

Product no.: 530E15A

Distance cutter, variable cutting length from 1.2 mm to 6 mm/
047 to .236 Inch

-  Special tool steel
-  ESD-safe
-  Variable cutting length (= V)



source images


The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 500 Micro is a full range of medium sized, robust, precision cutters with a wide range of head shapes. The cutters are manufactured from high grade tool steel. The cutting edges are hardened to Rockwell 63-65 HRC. The precision cutters have a nonreflecting surface, are ESD safe and resharable.

THE PERFECT CUT

Strong, sharp and precise - every time

- + 1 Million Movements**
Magic Spring™ design enables maximum durability with constant spring force movements
- + Quality**
Uncompromising Swiss quality created to be strong, durable and sharp
- + Precision**
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap
- + Strong and Sharp**
Hand-crafted cutting edges for superior strength and sharpness
- + Comfort, Security and Grip**
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology
- + ESD Safe**
Made from ESD-safe material to prevent damage to sensitive components

 Swiss Made

weller-tools.com **Weller**
Erem





Technical Data

Length mm	125
Length of cutting edges mm	---
Head width mm	11
Head thickness mm	6
Head length mm	29.0
Max. cutting capability – hard wire mm	---
Weight in oz	2.681
Length of cutting edges Inches	---
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	1.142
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	---
Max. cutting capability – copper wire mm	Ø 1.2
Length inches	4.921
Weight in g	76
Erem applications	---