






# 530E18

Product no.: 530E18

Distance cutter, cuts wire to a length of 1.8 mm/.070 Inch

-  Special tool steel
-  ESD-safe
-  Fixed cutting length



[source images](#)


## The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 500 Micro is a full range of medium sized, robust, precision cutters with a wide range of head shapes. The cutters are manufactured from high grade tool steel. The cutting edges are hardened to Rockwell 63-65 HRC. The precision cutters have a nonreflecting surface, are ESD safe and resharable.

## THE PERFECT CUT

Strong, sharp and precise - every time

- + 1 Million Movements**  
Magic Spring™ design enables maximum durability with constant spring force movements
- + Quality**  
Uncompromising Swiss quality created to be strong, durable and sharp
- + Precision**  
Experience precise cuts from the high-precision screw joint that enables a smooth action with no jaw overlap
- + Strong and Sharp**  
Hand-crafted cutting edges for superior strength and sharpness
- + Comfort, Security and Grip**  
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology
- + ESD Safe**  
Made from ESD-safe material to prevent damage to sensitive components

 Swiss Made

weller-tools.com **Weller**  
Erem





**Technical Data**

|  |       |
|--|-------|
| Length mm                                    | 120   |
| Length of cutting edges mm                   | ---   |
| Head width mm                                | ---   |
| Head thickness mm                            | ---   |
| Head length mm                               | ---   |
| Max. cutting capability – hard wire mm       | ---   |
| Weight in oz                                 | 2.469 |
| Length of cutting edges Inches               | ---   |
| Head width Inches                            | ---   |
| Head thickness Inches                        | ---   |
| Head length Inches                           | ---   |
| ESD-safe                                     | on    |
| Cut  | Flush |
| Max. cutting capability – medium hardness mm | ---   |
| Max. cutting capability – copper wire mm     | Ø 1,2 |
| Length inches                                | 4.724 |
| Weight in g                                  | 70    |
| Erem applications                            | ---   |