






554A

Product no.: 554A

Forming pliers for component connections, U-shape, axial forming.

-  Suitable for component connections, U-shape, axial forming
-  Narrow head shape.
-  ESD-safe



source images

Built to Last - Longest lasting durability on the planet

Weller Erem™ Pliers are designed to ensure an accurate and sure grip every time. Manufactured with uncompromising Swiss quality and created for worldwide applications, including electronics assembly and healthcare, Weller Erem Pliers are built to last. Feel the difference with Weller Erem™ – the proven choice. Every time.

BUILT TO LAST

Longest lasting durability on the planet

- + Quality**
Uncompromising Swiss quality created to be strong and durable
- + Precision**
Experience precise bending from the high-precision screw joint that enables a smooth action with no jaw overlap
- + 1 Million Movements**
Magic Spring™ design enables maximum durability with constant spring force movements
- + Comfort, Security and Grip**
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology
- ESD Safe**
Made from ESD-safe material to prevent damage to sensitive components



weller-tools.com **Weller**
Erem



PRECISION
TOOLS



Technical Data

Length mm	120
Jaw length in mm	23
Head width mm	---
Head thickness mm	---
Width of tips in mm	4
Total height of both tips in mm	6.4
Length inches	4.724
Jaw length inches	0.905
Head width Inches	---
Head thickness Inches	---
Width of tips in Inches	0.157
Total height of both tips in Inches	0.252
ESD-safe	on
Erem applications	---
Material	High grade tool steel
Weight in g	70
Weight in oz	2.469