







554E

Product no.: 554E

Forming pliers for component connection, U-shape.

-  Safe bending, forming and preparation of component connections
-  Non-reflecting surface
-  ESD-safe



[source images](#)

Built to Last - Longest lasting durability on the planet

Weller Erem™ Pliers are designed to ensure an accurate and sure grip every time. Manufactured with uncompromising Swiss quality and created for worldwide applications, including electronics assembly and healthcare, Weller Erem Pliers are built to last. Feel the difference with Weller Erem™ – the proven choice. Every time.

BUILT TO LAST

Longest lasting durability on the planet

+ Precision
Experience precise bending from the high-precision screw joint that enables a smooth action with no jaw overlap

+ Quality
Uncompromising Swiss quality created to be strong and durable

+ 1 Million Movements
Magic Spring™ design enables maximum durability with constant spring force movements

+ Comfort, Security and Grip
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology

ESD Safe
Made from ESD-safe material to prevent damage to sensitive components



weller-tools.com **Weller**
Erem



PRECISION
TOOLS



Technical Data

Length mm	120
Jaw length in mm	13
Head width mm	---
Head thickness mm	---
Width of tips in mm	10
Total height of both tips in mm	10
Length inches	4.724
Jaw length inches	0.513
Head width Inches	---
Head thickness Inches	---
Width of tips in Inches	0.394
Total height of both tips in Inches	0.394
ESD-safe	on
Erem applications	---
Material	High grade tool steel
Weight in g	70
Weight in oz	2.469