



543E

Product no.: 543E

Round nose pliers with very precise, smooth jaws.



Pliers for miniature and standard electronics



Non-reflecting surface, ESD-safe



Suitable for forming, bending, laying and feeding in wires.



[source images](#)

Built to Last - Longest lasting durability on the planet

Weller Erem™ Pliers are designed to ensure an accurate and sure grip every time. Manufactured with uncompromising Swiss quality and created for worldwide applications, including electronics assembly and healthcare, Weller Erem Pliers are built to last. Feel the difference with Weller Erem™ – the proven choice. Every time.

BUILT TO LAST

Longest lasting durability on the planet

+ Quality
Uncompromising Swiss quality created to be strong and durable

+ Precision
Experience precise bending from the high-precision screw joint that enables a smooth action with no jaw overlap

+ 1 Million Movements
Magic Spring™ design enables maximum durability with constant spring force movements

+ Comfort, Security and Grip
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology

ESD Safe
Made from ESD-safe material to prevent damage to sensitive components



weller-tools.com

Weller
Erem





Technical Data

Length mm	120
Jaw length in mm	20.5
Head width mm	11
Head thickness mm	6
Width of tips in mm	Ø 0,8
Total height of both tips in mm	1.6
Length inches	4.724
Jaw length inches	0.807
Head width Inches	0.433
Head thickness Inches	0.236
Width of tips in Inches	0.031
Total height of both tips in Inches	0.063
ESD-safe	on
Erem applications	Microelectronic
Material	Special tool steel
Weight in g	66.4
Weight in oz	2.342