

## Full HD Time Lapse Camera TX-164

Battery operated, for indoor and outdoor use



1080P Video

2MP Photo (1920x1080)

110° Field of View

2.4" TFT Color-Display

Operating with Batteries

Built-in Microphone & Speaker

Working Time 6 months

MicroSD Storage

IP66 Protection Class

- Time lapse camera battery operated for indoor and outdoor use
- Ideal for time lapse recordings of constructions sites, house building, plant growth (garden, orchard), outdoor shots, security monitoring, etc.
- Coloured time-lapse recordings during the day; Time-lapse recordings at night with high brightness additional by built-in LED (range ~18m)
- Select functions: time lapse photo, time lapse video, photo or video, stop motion
- MicroSD card\*\* up to 512GB (\*\*not included)
- Camera protection class IP56 (dust proof & heavy splash water proof)

### Technical Specifications:

- Image sensor: 1/ 2.7" CMOS 2MP (low-light)
- Lens: f=4mm, F/NO1.4, FOV=110°, Auto IR filter
- Video resolution: 1920x1080/25fps, 1280x720/30fps
- Photo resolution: 2MP (1920x1080), 1MP (1280x720)
- File format JPEG / AVI
- Exposure: +3.0EV ~-3.0EV in increments of 1.0EV
- Video length: 3sec.- 120sec. programmable
- Time lapse interval Custom: 3 seconds up to 24 hours; Mon-Sun
- Power supply: 12x AA batteries\* (\*included); external DC6V/1A\*\* [\*\*not included]
- Device language: EN, DE, SP, FR, IT, NL, FI, SE, DK, PO
- Working temperature: -20°C up to +50°C
- Weight / Dimensions: 378g (without batteries) / (L) 12.5 x (W) 8 x (H) 15cm

### Package Contents:

Full HD Time Lapse Camera TX-164, MicroUSB cable, Mounting belt, Rope, Wall bracket, Mounting bracket, 3x screws & 3x dowels, 12x AA batteries, User Manual



Article No. 4922

