



Digital Photo Frame

Realiview 7" APF700

- Photo Display
- Clock
- Calendar
- 7" LED Screen
- Memory formats : SD, SDHC, MMC, USB
- Energy saving : Programmable Auto On/Off



Realiview 7" APF700

- Photo Display
- Clock
- Calendar
- 7" LED Screen
- Energy saving : Programmable Auto On/Off



Product Dimensions	203*141*22 mm
Color	Black
Memory Nor flash	8MB
Display size	7 Inch
Display material	LED
Display ratio	16:9
Resolution	1024*600
Ac-adapter	5V1000mA - 100V-240V
Extension type	Support SD, SDHC, MMC, U-disk and so on, up to 32GB
Interface type	USB 2.0
Photo format	JPEG/JPG, BMP
Audio format	NO
Video format	NO
Slide show & speed	3s/5/10s/15s/1m ect, should be choose
Open/ Insert auto-play	On/Off, or auto-play photo when open or insert a memory card
Repeat mode	Single file, directory, all files
Speaker	NO

Operation	Key switch
Features	O'clock, calendar with slideshow, time switch, 360 Rotate, wall-hung
Languages	English, French, German, Italian, Spanish, Portuguese, Dutch, Russian, Polish, Hungarian, Czech
Accessories	Ac-adapter, Quick start guide, Stand
Net weight	0.35KG
Dimensions	205 x 143 x 23 mm
Packaging size	280 x 172 x 58 mm
Model	EAN
APF700	3760265541782
Packing	4 pieces

Manufactured for and distributed by GT COMPANY
5 rue de la Galmy • 77700 Chessy • France • www.gtcompany.fr

AgfaPhoto is used under licence of Agfa-Gevaert NV. For this product a sub-licence has been granted by AgfaPhoto Holding GmbH (www.agfaphoto.com). Neither Agfa-Gevaert NV nor AgfaPhoto Holding GmbH manufacture this product or provide any product warranty or support. For service, support and warranty information, contact the distributor or manufacturer.