



Action Camera

Realimove AC7000

- TRUE 2.7K Video – 30FPS
- 120° Wide Angle
- Dual Screen 2" + 1.3"
- Waterproof Case 30m
- Wifi
- Lithium Battery



Realimove AC7000

- TRUE 2.7K Video – 30FPS
- 120° Wide Angle
- Dual Screen 2" + 1.3"
- Waterproof Case 30m
- Wifi
- Lithium Battery



DSP	V3 ARM @ Cortex-A7 1.2GHZ / H.264
Image Sensor	OV8838 - 8M CMOS
Video Resolution	4K (3840*2160) @30fps (interpolation) 2.7K (2688*1520) @30fps 1080P (1920*1080) @60fps/30fps 720P (1280*720) @120fps/60fps/30fps
Photo Resolution	16MP (4608x3456) 12MP (4000x3000) 8MP (3264x2448) 5MP (2592x1936) 2MP (1600*1200)
Lens FOV	120° wide lens
LCD Display	2.0inch IPS+1.3inch TFT display
WIFI Function	802.11b/g/n
Extended storage	Support up to 64G Micro SDHC
HDMI Output	No
USB Port	Micro USB port, USB 2.0
Voice recorder	Yes
Speaker	Yes
Power input	5V 1A
Battery Capacity	3.7V Lithium Battery 750mAh
Charging Time	2 hours
Dimensions/Weight	59.3x29.3x41.1mm / 58 g
Languages	English, French, German, Spanish, Italian, Portuguese, Dutch, Polish, Czech, Hungarian, Russian
File Format	Video: MP4(H.264) Photo: JPG

Drama shot/timing shot	Yes
Slow Motion	Yes
Time-Lapse function	Yes
Loop recording	Yes
Driving record	Yes
Power saving function	Yes
USB mode	Support Mobile disk / Charging
Application for Smartphone	iOS, Android compatible



Model	EAN
AC7000	3760265541768

Manufactured for and distributed by GT COMPANY
5 rue de la Galmy • 77700 Chessy • France • www.gtcompany.fr

AgfaPhoto is used under licence of Agfa-Gevaert NV. For this product a sub-licence has been granted by AgfaPhoto Holding GmbH (www.agfaphoto.com).
Neither Agfa-Gevaert NV nor AgfaPhoto Holding GmbH manufacture this product or provide any product warranty or support. For service, support and warranty information, contact the distributor or manufacturer.