


Heat shrink butt crimp connectors waterproof assortment 340 pcs



SPECIFICATIONS

Red:	150PCS
Blue:	100PCS
Yellow:	20PCS
White:	50PCS
Black:	20PCS

Type: 2011C397

Picture	Color	Cable Size		Size (mm)		Maximum current
		AWG	mm ²	Diameter	Length	
	Yellow	12 ~ 10	4 ~ 6	6,9	42	48 A
	Blue	16 ~ 14	1,5 ~ 2,5	5,7	37	27 A
	Red	22 ~ 18	0,5 ~ 1,5	4,7	36	19 A
	Black	14 ~ 12	2,5 ~ 4	6	38	35 A
	White	26 ~ 24	0,3 ~ 0,5	4	26	9 A

Content: Red: 150 pcs, Blue: 100 pcs, White: 50 pcs, Yellow: 20 pcs, Black: 20 pcs.
Working temperature: -55 °C ... 125 °C. Shrink-temp.: 80 ... 130 °C. Voltage: max. 600 V.
UL-, CE- and RoHS-compliant. Please take care for a proper cable connection!

Connection only by qualified electricians. We assume no liability or warranty in case of incorrect application.



QUADRIOS

TECHNICAL DATA SHEET

www.quadrios.de