

Heat shrink solder seal sleeve connectors (2:1) 120 pcs assortment box

Picture	Color	QTY	Cable Size		Size (mm)	
			AWG	mm ²	Diameter	Length
 <p>6,0 mm 0.24in</p> <p>40 mm / 1.57in</p>	Yellow	20 pcs	12 ~ 10	4,0 ~ 6,0	6	40
 <p>4,5 mm 0.10in</p> <p>40 mm / 1.57in</p>	Blue	40 pcs	16 ~ 14	1,5 ~ 2,5	4,5	40
 <p>2,7 mm 0.1in</p> <p>40 mm / 1.57in</p>	Red	40 pcs	22 ~ 18	0,5 ~ 1,0	2,7	40
 <p>1,7 mm 0.05in</p> <p>26 mm / 1.02in</p>	White	20 pcs	26 ~ 24	0,25 ~ 0,34	1,7	26

- Type: Heat shrink solder sleeve 2011C396
- Color: White / Red / Blue / Yellow
- Waterproof when used correctly
- Minimum fully insulated temperature: 80 °C
- Fully melt temperature of solder: appx. 160 °C
- Minimum melt temperature of solder: 138 °C
- Shrinkage temperature: 138 °C ~ 160 °C
- Voltage resistance: 600 V
- Working temperature: -55 °C ~ 125 °C



Notice: Max. current limited by cable-diameter, cable-material and quality of the soldering joint!

Connection only by qualified electricians. We assume no liability or warranty in case of incorrect application.