

Data Sheet

D-Sub 9 Connector with CAN Termination



Technical data

Connector: D-Sub 9, male to female

Bus Termination: 120Ohm

Resistor: Between pin 2 and pin 7

Pin allocation: 1-to-1

Insulator: PBT glass fiber reinforce

Contact: Brass

Contact plating: Gold plated over nickel

Shell: Tin plated shell

Current rating: 3 A

Dielectric strength: 500 V AC for 1 minute

Insulator resistance: 500 M Ohm min. at 500 V DC

Operating Temperature: -40°C-80°C

Dimensions

All dimensions are in mm.

