

RLP73K2BR39JTD

✓ ACTIVE

CGS | CGS RLP73

TE Internal #: 3-2176056-9

CGS RLP73, Surface Mount Resistors, Current Sensing Resistor, 2

Termination, 1206, Taped & Reeled, 5 %, Thick Film, Resistance

Class Up to 1kΩ, .39 Ω

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors > Thick Film Resistor: Current Sense



Resistor Type: **Current Sensing Resistor**

Number of Terminations: **2**

Package Size Code: **1206**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **5 %**

[All Thick Film Resistor: Current Sense \(156\)](#)

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Current Sensing Resistor
Package Size Code	1206
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Passive Component Tolerance	5 %
Resistance Class	Up to 1kΩ
Resistance Value	.39 Ω
Power Rating	.5 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Passive Component Dimensions	3.1 x 1.55 x .55 mm
------------------------------	---------------------



Usage Conditions

Temperature Coefficient	±200 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-C339-R529A
Thick Film Resistor: Current Sense

TE Part # CAT-C339-R529C
Thick Film Resistor: Current Sense



Also in the Series | CGS RLP73

Surface Mount Resistors(396)

Customers Also Bought

TE Part #T4171110003-001
M12 Panel Mount Wire

TE Part #1623781-3
Wirewound Resistor: Vertical Mount

TE Part #1-215297-6
16P HV100 REC CON. TE, 7.0MM

TE Part #1-1825059-3
ADF04S04=DIP SWT,FLUSH,SMT-GW

TE Part #1-84534-6
1.25mm FPC Connectors

TE Part #1217062-1
187 FASTON,FLAG,PCB TAB,TNBR

TE Part #1622264-1
LR0204 1% 62K

TE Part #1-1903328-4
DYNAMIC 4000 HDR ASSY

TE Part #1461373-9
STD OEG Miniature PCB OJT Power Relays

TE Part #1-2176251-2
CRGS2010 5% 8R2

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_3-2176056-9_BA.2d_dxf.zip
- English
- Customer View Model



[ENG_CVM_CVM_3-2176056-9_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-2176056-9_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD Low Ohmic Current Sense Resistors - Type RL73 Series

English