

PKS1106B1/4 ✓ ACTIVE

[Alcoswitch](#) | [Alcoswitch PKS](#)

TE Internal #: 9-1437624-7

Alcoswitch PKS, Switch Knobs, Knob, Phenolic, Straight Knurl Knob Design, .25in [6.35mm] Shaft Size, 1.17in [29.7mm] Switch Knob Diameter, Black, Line

[View on TE.com >](#)



Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**

Switch Knob Material: **Phenolic**

Knob Design: **Straight Knurl**

Shaft Size: **6.35 mm [.25 in]**

Switch Knob Diameter: **29.7 mm [1.17 in]**

Features

Product Type Features

| | |
|--------------------------|------|
| Switch Knob Product Type | Knob |
|--------------------------|------|

Configuration Features

| | |
|-------------|----------------|
| Skirt | With |
| Spinner | Without |
| Spin Plate | Without |
| Knob Design | Straight Knurl |

Body Features

| | |
|----------------------|----------|
| Switch Knob Material | Phenolic |
| Switch Knob Color | Black |

Dimensions

| | |
|----------------------|------------------|
| Shaft Size | 6.35 mm[.25 in] |
| Switch Knob Diameter | 29.7 mm[1.17 in] |

Identification Marking

| | |
|--------------------|----------|
| Indicator Style | Line |
| Indicator Location | On Skirt |

Other

| | |
|---------|-------------------------|
| Comment | Top spun aluminum inlay |
|---------|-------------------------|



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | [Alcoswitch PKS](#)



Switch Knobs(7)

Customers Also Bought



TE Part #1744429-4
3.96 EP HDR ASSY 4P W/PEGS, GW



TE Part #1393255-6
W93-X112-25=M6/M7/M9/W6/W7



TE Part #1-84534-4
1.25mm FPC Connectors



TE Part #1-745497-6
IDC D-Sub: Receptacle Assembly, Wire to Wire, Signal, 2.77 mm



TE Part #2-1437558-7
MTA206R=(MSTA) SW TOG DPDT



TE Part #1551246-2
Double row 10P BtB connector



TE Part #CB5060-000
BSTS-20X4



TE Part #1437625-5
PKS90B1/4=KNOB PLASTIC W/SKIRT



TE Part #1551120-5
1 piece BtB connector 0.7mm



TE Part #1648318-2
702-32-01109=CONTACT,SKT,#12

Documents

Product Drawings

[PKS1106B1/4=KNOB PLASTIC W/SKI](#)

English

CAD Files

[3D PDF](#)

[3D](#)

Customer View Model

[ENG_CVM_CVM_9-1437624-7_A_c-9-1437624-7-a.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_9-1437624-7_A_c-9-1437624-7-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1437624-7_A_c-9-1437624-7-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English