

Corcom IK

TE Internal #: 6609973-2

TE Internal Description: 35IK10=F4027Z

CORCOM IK SERIES SINGLE PHASE FILTERS

[View on TE.com >](#)

All CORCOM IK SERIES SINGLE PHASE FILTERS (1)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Corcom IK



Single Phase Filters(1)

Customers Also Bought



TE Part #3-640706-1
Wire-to-Board Connector Contacts:
socket, wire size 30-16 AWG, SL 156



TE Part #640250-3
3.96mm Wire-to-board housing:
receptacle, with mating alignment, SL
156



TE Part #2-34161-1
TERMINAL,PG R 16-14 10



TE Part #2-320553-2
PIDG RING TONGUE TERMINALS



TE Part #5069834023
Single Wall CGPT Spool Heat Shrink
Tubin



TE Part #521633-2
ULTRA POD: Flag, Receptacle
Assembly, Tin Plated, .250 inch



TE Part #5666293001
CLFH179(S50)



TE Part #8-6609087-8
F7247Y=6AMP, 480VAC

Documents

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE_IK_SERIES](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English