1-1337435-0 × OBSOLETE

TE Internal #: 1-1337435-0

TE Internal Description: BNC RM BHJ Hex 75Ohm Nickel Pltd RG59B/U

View on TE.com >

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Customers Also Bought



TE Part #165049
PIDG FORMED WIRE PINS



TE Part #1879073-6
Power Resistor: Aluminum Housed, 75 Watt



TE Part #165805-000
D-602-0144

TE Part #1534805-1
HD20 COVER KIT 9POS WITH CABLE

TE Part #W4S-P012
DEUTSCH DT WEDGELOCKS

TE Part #1-1418639-5
MQS, CONNECTOR HOUSING

TE Part #1SNA205396R0300
HD10/12.F5.2

TE Part #1SNA295396R2500
HD10/12.F5.2

Documents

CAD Files

3D PDF

3D

Customer View Model
ENG_CVM_CVM_1-1337435-0_D.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1-1337435-0_D.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1-1337435-0_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Economy RF Coaxial Connectors

English

Product Specification

English