




Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Covers



Connector Cover Type: **Strain Relief**  
Number of Positions: **50**  
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

|                      |               |
|----------------------|---------------|
| Product Type         | Accessory     |
| Connector Cover Type | Strain Relief |

Configuration Features

|                     |    |
|---------------------|----|
| Number of Positions | 50 |
|---------------------|----|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |
|-----------------------------|----------------------------|

Packaging Features

|                    |              |
|--------------------|--------------|
| Packaging Method   | Kit, Package |
| Packaging Quantity | 100          |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                         |
|-----------------------------------------------|-----------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                               |
| EU ELV Directive 2000/53/EC                   | Compliant                               |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006        |                                         |



Current ECHA Candidate List: JAN 2021 (211)  
Candidate List Declared Against: JAN 2021 (211)  
Does not contain REACH SVHC

|                           |                                                                                            |
|---------------------------|--------------------------------------------------------------------------------------------|
| Halogen Content           | Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability                                               |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-357-D658  
IDC D-Sub: Plug Assembly, Signal, Cable to Cable, 2.16 mm

Also in the Series | CHAMP Docking Connectors



D-Sub Covers(27)



D-Sub Locking & Mounting(31)



Docking Connector Guide Hardware(5)



Docking Connectors(33)



IDC D-Sub Connectors(85)



PCB D-Sub Connectors(1)

Customers Also Bought



TE Part #1658654-1  
D-Sub Crimp Recpt Signal 9 Posn,  
Socket Size 20, Shell Size 1



TE Part #1-440054-1  
AMP HPI 2.0MM HEADERS



TE Part #103653-1  
02 MTE SHRD PIN HSG SR LATCH



TE Part #770902-1  
MINI UMNL SOCK 26-22 AWG SN



TE Part #172213-7  
EIS CAP HSG PANEL MOUNT 7P  
NATUTURAL




TE Part #1903977-1  
SLIM UPM 4POS. R/A HDR ASSEMBL



TE Part #1-5221128-7  
PLUG,COMMERCIAL BNC



TE Part #1-770253-0  
UMNLI SOK PTPPHBZ LP LF 24-18



TE Part #1-552027-1  
STRAIN RELIEF, 50 POS, CHAMP

Documents

Product Drawings  
KIT, COVER, 180, 50 POS  
English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_2-552008-1\_P.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-552008-1\\_P.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-552008-1\\_P.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Product Environmental Compliance**

**TE Material Declaration**

English