



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | LUMAWISE Endurance N




ANSI Street Lighting Accessories(17)




ANSI Street Lighting Base Assemblies (14)



ANSI Street Lighting Power Management(6)



ANSI Street Lighting Receptacles(25)



Street Lighting Open & Shorting Caps (3)

Customers Also Bought



TE Part #6609027-5
CORCOM K SERIES SINGLE PHASE FILTERS




TE Part #2315539-1
PHOTO CONTROL COVER



TE Part #1-1734595-5
AMP HPI 1.0MM HEADERS



TE Part #1-2337216-2
RAIN-SKIRT, LUMAWISE ENDURANCE S, LT GRY



TE Part #2842142-5
10P,2MM,BRK HDR,DRV,T,SMD,0.1AU, TR W/CAP



TE Part #2842142-7
14P,2MM,BRK HDR,DRV,T,SMD,0.1AU, TR W/CAP



TE Part #1624116-4
BMB-B 0603 120R



TE Part #3-1879499-9
CRGH2010 5% 39R 1W



TE Part #2306130-2
COVER, LIGHT CONTROLLER, 81MM DIA., MED

Documents



CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2306133-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2306133-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2306133-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[LUMAWISE ENDURANCE N CONTROL BASE, SLEEVE AND COVER](#)

English

[LUMAWISE ENDURANCE N CONTROL BASE, SLEEVE AND COVER](#)

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Dimmable Photocontrol CB Test Report](#)

English

[Dimmable Photocontrol CB Certificate](#)

English