211883-5 ✔ ACTIVE


AMPLIMITE

TE Internal #: 211883-5

D-Sub Locking & Mounting, Male Screwlock Assembly, Screw Length .357 in [9.08 mm]

View on TE.com >

Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Male Screwlock Assembly**

Screw Length: **9.08 mm [.357 in]**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Male Screwlock Assembly

Mechanical Attachment

Screw Material	Stainless Steel
Screw Finish	Passivated
Screw & Hole Thread Size	4-40 UNC 2A
Screw Length	9.08 mm[.357 in]

Operation/Application

For Use With	Metal Shell Connectors

Packaging Features

Packaging Quantity	1
Packaging Method	Individual, Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211)

	Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Customers Also Bought



TE Part #2-320571-4
PIDG RING TONGUE TERMINALS




TE Part #1-1757824-1
AMPLIMITE,ASY,RCPT,STD,90,ZN,5,CT



TE Part #1-1617749-2
FCA-210-1015M=M83536/10-015M



TE Part #1617122-2
JMACD-12XM = M39016/15-079M



TE Part #109858-000
D-181-1222-90/9



TE Part #1490406-1
HYP10 TERMINYL 2AWG DIE SET



TE Part #1757835-4
AMPLIMITE,PLUG ASY,R/A,109,ZN,4

TE Part #YDJT14F25-35SNV001
PLUG ASSY

TE Part #11029042-00
44019A T-LINEAR COMPONENTS

TE Part #1-1618279-3
MHC-1=RELAY, VACUUM, SPDT

Documents

Product Drawings

SCREW RETAINER KIT,AMPLIMITE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_211883-5_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_211883-5_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_211883-5_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Environmental Compliance

TE Material Declaration

English