# 1-964576-1 ✔ ACTIVE

RAST

TE Internal #: 1-964576-1

PCB Connector Mounting, PCB Frame, 11 Position, 2.5mm [.098in] Centerline, Black, Printed Circuit Board

View on TE.com >

Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Hardware > Mounting







Connector Mounting Accessory Type: **PCB Frame**

Number of Positions: **11**

Centerline (Pitch): **2.5 mm [ .098 in ]**

Primary Product Color: **Black**

Connector & Contact Terminates To: **Printed Circuit Board**

## Features

### Product Type Features

| | |
|---|---|
| Connector Mounting Accessory Type | PCB Frame |
| Connector & Contact Terminates To | Printed Circuit Board |

### Configuration Features

| | |
|---|---|
| PCB Mount Orientation | Vertical |
| Number of Positions | 11 |

### Body Features

| | |
|---|---|
| Primary Product Color | Black |

### Housing Features

| | |
|---|---|
| Centerline (Pitch) | 2.5 mm[.098 in] |

### Dimensions

| | |
|---|---|
| PCB Thickness (Recommended) | 1.5 mm[.059 in] |

### Industry Standards

| | |
|---|---|
| UL Flammability Rating | UL 94V-0 |

### Packaging Features

| | |
|---|---|
| Packaging Quantity | 3000 |
| Packaging Method | Carton |

## Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


## Compatible Parts



TE Part # 2-2232891-1
11P MONOPLUG 2.5 SELECTIVELY LOADED




TE Part # 1-284931-1
DUOPLUG Standard, female conn.



TE Part # 1-293207-1
DUOPLUG Std conn.,11 pos,gwt750 v0



TE Part # 1-964576-7
DUOPLUG2,5RAHMEN17P



TE Part # 2-293207-1
DUOPLUG Std.,11 pos,gwt750



TE Part # 2-964576-7
DUOPLUG2,5RAHMEN17P



TE Part # 5-1534799-1
AMP DUOPLUG MARK II CONNECTOR SELE.LOAD



TE Part # 9-964575-3
DUOPLUG2,5RAHMEN 3P

TE Part # 1-2304528-1
AMP DUOPLUG MK2 CONNECTOR 11P SELECTIVE

TE Part # 1-284930-1
DUOPLUG Standard, female conn.

TE Part # 2-2304528-1
AMP DUOPLUG MK2 CONNECTOR 11P SELECTIVE

TE Part # 2304528-1
AMP DUOPLUG MK2 CONNECTOR 11P SELECTIVE

TE Part # 3-2304528-1
AMP DUOPLUG MK2 CONNECTOR 11P SELECTIVE

TE Part # 2-1534799-1
AMP DUOPLUG 2.5 MK-II 11P SELEC. LOADED

## Customers Also Bought



TE Part #1-917266-3
DYNAMIC 3200 REC AND TAB HSG



TE Part #175288-3
DYNAMIC 3000 CONTACT



TE Part #1-917657-3
DYNAMIC 3200 HDR ASSY



TE Part #170048-2
110 FASTON,REC.,24-20 AWG,TPBR



TE Part #1318577-1
DYNAMIC 2000 REC AND TAB HSG



TE Part #2151018-1
OCEAN_2.0_APPLICATOR-S-090F110F

## Documents

## CAD Files

### 3D PDF

3D

**Customer View Model**

ENG_CVM_CVM_1-964576-1_Z_c-1-964576-1-z.2d_dxf.zip

English

**Customer View Model**

ENG_CVM_CVM_1-964576-1_Z_c-1-964576-1-z.3d_igs.zip

English

**Customer View Model**

ENG_CVM_CVM_1-964576-1_Z_c-1-964576-1-z.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

## Datasheets & Catalog Pages

### 1654742_HOUSEHOLD_APPLIANCES_RAST5

English

## Agency Approvals

### Agency Approval Document

English