
1-552296-1 ✔ ACTIVE

CHAMP Docking Connectors

TE Internal #: 1-552296-1

TE Internal Description: STRAIN RELIEF 64 POS BLACK

View on TE.com >



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Also in the Series | CHAMP Docking Connectors



D-Sub Covers(27)



D-Sub Locking & Mounting(31)



Docking Connector Guide Hardware(5)



Docking Connectors(33)



IDC D-Sub Connectors(85)



PCB D-Sub Connectors(1)


Customers Also Bought



TE Part #229975-1
IDC D-Sub: Receptacle Assembly, Signal, 2.16 mm



TE Part #2-323914-1
PIDG RING TONGUE TERMINALS



TE Part #207470-1
CABLE CLAMP KIT,SZ 2



TE Part #1423157-2
7012AB=RLY,STD,ON,2P,120VAC,5S



TE Part #229969-1
COVER,DUST,RCPT,RED,CHAMP



TE Part #229968-1
COVER,DUST,PLUG,BLUE,CHAMP



TE Part #229969-2
COVER, DUST, RCPT, RED, CHAMP



TE Part #1062-16-0622
DEUTSCH STAMPED & FORMED CONTACTS

TE Part #DT3P-BT-BK
BOOT, 3P, REC, ST, BLK

TE Part #229622-1
CLAMP, CABLE, PALM GRIP

Documents

Product Drawings

STRAIN RELIEF 64 POS BLACK

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1-552296-1_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-552296-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_1-552296-1_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Instruction Sheets

Instruction Sheet (U.S.)

English