SETR14AI-TINEL-LOCK-RING ✔ ACTIVE

Raychem

TE Internal #: CZ3662-000

Screened Backshells & Adapters, Tinel-Lock Ring, 36 Single

View on TE.com >

Connectors > Connector Backshells & Adapters > Screened Backshells & Adapters



Termination Device Type: **Tinel-Lock Ring**

Braid Type: **36 Single**

Features

Product Type Features

Termination Device Type	Tinel-Lock Ring

Configuration Features

Braid Type	36 Single

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 173643-000
RH-3960-1-TINEL-KIT-120V


Customers Also Bought




TE Part #212510-1
RECEPT ASSY,SZ 17C2,AMPLIMITE



TE Part #183253-000
TXR18AB00-2214AI



TE Part #462378-000
Low Profile Heat Shrink Boots: Poly Mold, Lipped, Right Angle



TE Part #625037-000
Low Profile Heat Shrink Boots: Blow Mold, Lipped, Right Angle



TE Part #YDTS26Z11-99PBV001
D38999: Straight Plug, 11-99 Insert




TE Part #1-1423153-0
2122AH1SG=RLY,MINI,OFF,2P,HER




TE Part #2280413-1
CCII TAB REC CONN 22-18 ASSY



TE Part #427691-000
55A1111-26-9-9CS2275



TE Part #CX9353-000
TX40AZ00-2016



TE Part #CX9375-000
TX40AZ00-2414

Documents

Product Drawings

SETR14AI-SIDE-ENTRY-TINEL-LOCK-RING

English

Datasheets & Catalog Pages

Circular Backshells

English

Product Specifications

General Information Package for Tinel-Lock Adapters

English

Assembly Guide for Raychem Side Entry Tinel-Lock Rings, Heat Recoverable for Braid Termination

English