



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1586037-6
6P VERT HDR VAL-U-LOK V2

TE Part #1-104480-6
SHORT POINT RECP CONT LP

TE Part #1-2834016-2
2POS 2.54MM SES CONN.

TE Part #1-2213767-5
AV19 SPM 5A MOVE RING LED GREEN 24V

TE Part #1437664-4
NC6-P107-02=NC6 ASSEMBLY

TE Part #103968-7
2X8 MTE RCPT SR RIBBED .100CL

TE Part #1-1879519-1
CRGH2010 1% 137R 1W

TE Part #1-499786-2
AMP-LATCH UNIVERSAL HEADERS

TE Part #YDTS24W17-06PAC001
Jam Nut: D38999, 17-06 Insert

TE Part #1-223969-0
UNV PWR MDL, GUIDE PIN LOCT PL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_5-1478996-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_5-1478996-5_A.3d_stp.zip

English

Customer View Model

ENG_CVM_5-1478996-5_A.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_CVM_5-1478996-5_A.2d_dxf.zip

English

Customer View Model



[ENG_CVM_CVM_5-1478996-5_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1478996-5_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English