



Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



 TE Part #1-2213767-5 AV19 SPM 5A MOVE RING LED GREEN 24V	 TE Part #1437664-4 NC6-P107-02=NC6 ASSEMBLY	 TE Part #1614929-2 CPF0805 3K3 0.1% 25PPM 5K RL	 TE Part #1-2176163-7 UPF50 0.1% 5PPM 50R
 TE Part #T4145535041-001 M12 Panel Mount PCB	 TE Part #1-1337448-0 BNC BHSkt + TAG 50Ohm Nickel Pltd	 TE Part #1-1478418-0 N R/A Plg PS 50Ohm Silver Pltd PSF 1 /4M,	 TE Part #1-1337455-0 BNC Str Adp PP 50Ohm Silver Pltd
 TE Part #1-1571987-5 A201J51ZQ0004=DBL POLE,ROCKER	 TE Part #1-1571987-9 A201J61ZQ0004=DBL POLE,ROCKER		

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_3-1478996-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_3-1478996-4_A.3d_stp.zip

English

Customer View Model

ENG_CVM_3-1478996-4_A.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_CVM_3-1478996-4_A.2d_dxf.zip

English

Customer View Model



[ENG_CVM_CVM_3-1478996-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1478996-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1307191 RF Coax Products Catalog](#)

English