

2317857-2 ✔ ACTIVE


TE Internal #: 2317857-2

OSFP, Accessory, Wire-to-Board

View on TE.com >

Connectors > Pluggable IO Connectors & Cages > OSFP




Pluggable I/O Product Type: **Accessory**

Connector System: **Wire-to-Board**

Sealable: **No**

Features

Product Type Features

Form Factor	OSFP
Pluggable I/O Accessory Type	Dust & EMI Cover
Cage Type	Kit
Pluggable I/O Product Type	Accessory
Connector System	Wire-to-Board
Sealable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # CAT-P65-N4903
OSFP Cage Assembly: EMI Springs

Customers Also Bought



TE Part #2042162-1
Right Angle Male Connector



TE Part #1888810-2
EMI/Dust Cover,XFP And QSFP




TE Part #103968-7
2X8 MTE RCPT SR RIBBED .100CL



TE Part #2214593-1
zQSFP+ STACKED RECEPTACLE ASSEMBLY 2X2



TE Part #1-1879519-1
CRGH2010 1% 137R 1W




TE Part #1-499786-2
AMP-LATCH UNIVERSAL HEADERS



TE Part #YDTS24W17-06PAC001
Jam Nut: D38999, 17-06 Insert



TE Part #1-223969-0
UNV PWR MDL, GUIDE PIN LOCT PL



TE Part #147377-1
10 SYS50 SMT HDR DR SHD W/O HD



TE Part #1625980-6
HSX25 R22 5%

Documents

Product Drawings

DUST AND EMI PLUG, PLATED, OSFP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2317857-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2317857-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2317857-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

OSFP Cages, Connectors, and Cable Assemblies (English)

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English