2120432-3 ✔ ACTIVE

MotorMan



TE Internal #: 2120432-3

MotorMan, Rectangular Backshells & Clamps, Cable Clamp, UL 94V-0

View on TE.com >

Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Backshells & Clamps



Backshell & Clamp Accessory Type: **Cable Clamp**

UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Backshell & Clamp Accessory Type	Cable Clamp

Industry Standards

UL Flammability Rating	UL 94V-0

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.7% in Component Part) **Article Safe Usage Statements:** Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

TE Part # 2083288-2

Also in the Series | MotorMan



Circular Connector Caps & Covers(1)



Circular Connector Contact Inserts(2)



Circular Connector Seals(1)



Rectangular Backshells & Clamps(3)



Rectangular Caps & Covers(1)



Rectangular Connector Hardware(2)



Rectangular Connector Hoods & Bases (4)



Rectangular Connector Locking(2)



Rectangular Connector Seals(1)



Rectangular Contact Inserts(5)



Rectangular Power Connectors(2)


Customers Also Bought



TE Part #2120337-1
SINGLE WIRE SEAL



TE Part #1103427-2
HC26.Bu.4.C.5,2



TE Part #2-160978-1
CABLE TY 360X4,8NAT



TE Part #2120330-1
METAL HOOD / KIT




TE Part #2120336-1
PROTECTION COVER



TE Part #206748-000
STD SNAP-ON MARKERS



TE Part #2120321-1
SIGNAL HOUSING 5 POS



TE Part #1-216792-0
AMP LATCH ASSY 10 PO

TE Part #1103426-1
MALE INSERT, CRIMP, 4-POS. 22DF CONTACTS

Documents

Product Drawings

CRIMP SLEEVE

English

Product Specifications

Product Specification

English