




Connectors > Modular Jacks & Plugs > Modular Jack & Plug Accessories > Modular Jack & Plug Caps & Covers



Modular Jacks & Plugs Accessory Type: **Closure Cap**

Modular Jack & Plug Interface Type: **RJ45**

Modular Jacks & Plugs Products: **Accessories**

Modular Connector Style: **Plug**

Shielded: **No**

Features

Product Type Features

Connectors & Connector Components Type	Accessory
Closure Cap Type	Plug Cordset
Modular Jacks & Plugs Accessory Type	Closure Cap
Modular Jack & Plug Interface Type	RJ45
Modular Jacks & Plugs Products	Accessories
Modular Connector Style	Plug
Connector & Contact Terminates To	Wire & Cable

Body Features

Cap Color	Black
Cap Material	Delrin
Cover Color	Black

Housing Features

Compatible With Connector Shape	Circular
---------------------------------	----------

Operation/Application

Shielded	No
----------	----

Packaging Features

Packaging Quantity	1, 25
Packaging Method	Bag, Package



Other

Lanyard	With, Without
Lanyard Length	92.2 mm[3.63 in]

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1546405-1 ETHERNET DIRECT PCB MNT RCPT	 TE Part # 1546413-3 ETHERNET RJ-45 BLKHD PASSTHRU	 TE Part # 1546414-4 ETHRNT RJ-45 BLKHD PASSTHRU12"	 TE Part # 1-1546412-1 ETHERNET RCPT W/PC BRD & CBL
---	--	---	---



TE Part # 1-1546409-1
ETHERNET RECEPTACL W/PC BOARD

TE Part # 1-1546411-1
ETHERNET RCPT W/PC BRD & CBL

TE Part # 1546641-1
THRD THRU PNL INTRCNCT,M40,IE

TE Part # 1-1546410-1
ETHERNET RCPT W/PC BRD & CBL

TE Part # 1-1546415-1
ETHERNET RJ-11 BLKHD PASSTHRU

TE Part # 1546574-1
RJ-LNXX FE TO FE ADAPTOR

Also in the Series | Industrial RJ45 Variant 3

Circular RJ45 Connectors(8)

Modular Jack & Plug Caps & Covers(3)

Customers Also Bought

TE Part #1658539-5
D-Sub Connector Contacts: Pin, Brass, Signal, Size 20

TE Part #1623782-9
Wirewound Resistor: Vertical Mount

TE Part #1546907-1
CPC PLG ASSY,IND ETHERNET,SHLD, SLD WR

TE Part #104482-5
12 SHORT PT RCPT HSG DR .100CL

TE Part #YDTS20F15-05SBV001
D38999: Square Flange, 15-05 insert

TE Part #1546440-1
ETHERNET FIELD ATTACHABL CONN

TE Part #1-104482-5
34 SHORT PT RCPT HSG DR .100CL

TE Part #148423-5
EURO TYPE M REC 42+6,THIN STK



TE Part #1-558693-1
IDC D-Sub: Plug Assembly, Signal,
Cable to Cable, 2.16 mm



TE Part #1-552027-1
STRAIN RELIEF, 50 POS, CHAMP

Documents

Product Drawings

ETHERNET CLOSURE CAP FOR CRDSET

English

Datasheets & Catalog Pages

INDUSTRIAL_ETHERNET_PRODUCTS

English