




Connectors > Lighting Connectors > Street Lighting Controls > Zhaga Book 18 Street Lighting Connectors > LUMAWISE Endurance S Domes



Lighting Product Type: **Connector**

Housing Color: **Gray**

Product Height: **39.25 mm**

Lighting Connector Features Included: **Keyed, Not Vented**

Agency/Standard: **Zhaga**

[All LUMAWISE Endurance S Domes \(13\)](#)

Features

Product Type Features

Lighting Product Type	Connector
Sealable	Yes

Configuration Features

Lighting Connector Features Included	Keyed, Not Vented
Number of Positions	1

Housing Features

Housing Color	Gray
---------------	------

Dimensions

Product Diameter	40 mm
Product Height	39.25 mm

Usage Conditions

IP Water Sealing Level	6
------------------------	---



IP Dust Sealing Level	6
Operating Temperature Range	-40 – 90 °C

Industry Standards

Agency/Standard	Zhaga
-----------------	-------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-L97-B2911
LUMAWISE Endurance S Base Assembly

Also in the Series | LUMAWISE Endurance S



Poke-In Connectors(1)



Zhaga Book 18 Street Lighting Connectors(32)

Customers Also Bought



TE Part #1473005-1
DDR2 SO DIMM Sockets



TE Part #1-2213871-1
PHOTO CONTROL BASE



TE Part #1-2328823-1
LUMAWISE Endurance S Domes



TE Part #2-160256-1
250 FASTON, REC., 17-14 AWG, BR



TE Part #1-2328823-2
LUMAWISE S 80MM DIA DOME CLEAR MEDIUM



TE Part #1-2328823-3
LUMAWISE S 80MM DIA DOME CLEAR TALL



TE Part #1-2329013-1
LUMAWISE 40MM DIA DOME CLEAR LOW



TE Part #T1230160132-100
H16B-TSH-M32



TE Part #1513164-1
MOLDED STAMPED ANTENNA



Documents

Product Drawings

LUMAWISE 40MM DIA DOME CLEAR TALL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2329013-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2329013-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2329013-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

LUMAWISE ENDURANCE Connector System

English

Lumawise Endurance S Modules

English

LUMAWISE STREET LIGHT DIMMING AND CONTROL QUICK REFERENCE GUIDE

English

Datasheet - Lumawise Z10

English

Product Specifications

Application Specification

English

Agency Approvals

LUMAWISE Endurance S CB Certificate

English

LUMAWISE Endurance S CB Test Report

English