



Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 188729-1
8P.COVER/SOLD.STOP

Also in the Series | AMP-METRIMATE



Card Edge Power Connectors(1)



Card Guide Hardware(1)



Portable Crimp Tools(1)



Rack & Panel Connectors(1)



Rectangular Power Connectors(9)



RF Connectors(1)



RJ45 Connectors(45)




SO DIMM Sockets(14)




Wire-to-Board Headers & Receptacles
(3)


Customers Also Bought



TE Part #5-1775855-1
RJ45 OVER USB W/ 6 PNL-GND & HTD G/F



TE Part #5552726-3
ASSY,PLUG,50 POSN, RTANG, PCB




TE Part #53833-1
SOLIS SPR SPADE 16-14 8



TE Part #500004-1
SPIRAP 1/4" FR PE, WHITE, 50FT






TE Part #54489-2

HSG ASSY,PWR LK,SRS1,2POS,FLNG




TE Part #2015698-2

C/A, UMCC/UMCC 0.80 OD CABLE, 100MM LONG



TE Part #8-2176315-2

MELF SMA-A 39R 1% 50PPM 0204 0.4 W



TE Part #5-2176315-6

MELF SMA_A 3K3 1% 50PPM 0204 0.4 W



TE Part #216415-4

128P.IEC-C FEM.CONN



TE Part #5536437-4

ASSY,PIN,EUROCARD,TYPE C,LEAD-FREE,96 PO

Documents

Product Drawings

STK MJ ASSY,8POS,2X1,SHLD,CAT5

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2007022-1_B1_c-2007022-1-b1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2007022-1_B1_c-2007022-1-b1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2007022-1_B1_c-2007022-1-b1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English