



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Customers Also Bought



TE Part #1735078-1
SAS PLUGS



TE Part #1903814-1
INDUSTRIAL USB REC ASSY R/A
1ROW




TE Part #1376133-2
DYNAMIC 3500 HDR ASSY



TE Part #1-178138-5
DYNAMIC 3200 HDR ASSY




TE Part #1-2271656-1
Mini I/O Straight Header Type 1



TE Part #9-2013519-0
DYNAMIC D3900 H-HDR ASSY 7/10P
Z TYPE-A



TE Part #1-2013519-3
DYNAMIC D3900 H-HDR ASSY 3P X
TYPE-A



TE Part #1-2013519-0
DYNAMIC D3900 H-HDR ASSY 10P X
TYPE-A



TE Part #1-2229794-1
D3950 REC 11POS 1ROW X KEY
MARKED



TE Part #1-2229803-1
D3950 HDR 11POS 1ROW X KEY

Documents

Product Drawings

INDUSTRIAL MINI I/O HDR ASSY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1981080-1_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1981080-1_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1981080-1_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages
[1-1773703-8_INDUSTRIAL_MINI_IO](#)

English
[1-1773703-8_MINI_IO](#)

English

Product Specifications
[Application Specification](#)

English

Product Environmental Compliance
[MD_1981080-1_07282017913_dmtec](#)

English
[MD_1981080-1_07282017913_dmtec](#)

English

Agency Approvals
[UL Report](#)

English