1393436-4 ✔ ACTIVE

TE Internal #: 1393436-4

TE Internal Description: V23542C1028B300=KABELBAUMST. 8

View on TE.com >



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 963531-1
BLINDSTOPFEN



TE Part # 964971-1
EINZELLEITERDICHTNG



TE Part # 2-1411573-1
ELOGED F5700Y75



TE Part # 963530-1
EINZELLEITERDICHTNG




TE Part # 2151388-1
OCEAN_2.0_Applicator-S-062F120O



TE Part # 2836345-1
OCEAN_2.0_Applicator-S-055F120O



TE Part # CAT-HPCH5372
HIGH PIN COUNT HEADER



TE Part # 1393454-5
V23542C1028Z300=ABDECKK 28PDIC

TE Part # 1412493-1
C23372A 13C310=28 POL KUL.NUT

TE Part # 1412495-1
C23372A 13C330=28 POL RADIALD

TE Part # 1412753-1
C23372A 13C320=28 POL SICHER.

TE Part # 4-1411572-1
ELOGEDR X5600Y75

Customers Also Bought



TE Part #1103427-2
HC26.Bu.4.C.5,2



TE Part #1-965640-5
TIMER, CONNECTOR HOUSING




TE Part #DT8S-BT-BK
BOOT, 8P, PLG, ST, BLK




TE Part #1393450-3
V23542C1052B102=52P KABELBAUM-




TE Part #1393450-5
V23542C1052B300=KABELBAUMST 80




TE Part #1393454-1
V23542C1028Z100=28P ABDECKKAPP




TE Part #1393457-4
V23540M1000Z110=DICHTTULLE (F1



TE Part #1393454-7
V23542C1052Z102=52P ABDECKKAPP



TE Part #1393454-9
V23542C1052Z300=ABDECKK 52PDIC



TE Part #1393454-5
V23542C1028Z300=ABDECKK 28PDIC

Documents

Product Drawings

V23542C1028B300=KABELBAUMST. 8

English

V23542C1028B300=KABELBAUMST. 8

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1393436-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1393436-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1393436-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.