



### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


### Customers Also Bought

TE Part #2273012-4  
M8 R/A LED PIGTAIL

TE Part #1954381-1  
Asy, Grounding Clip, 10-12 AWG S

TE Part #36499  
TERMINAL, SOLIS R 8 3/8

TE Part #970155-000  
44AM1111-20-9-9CS2275




TE Part #1-796949-8  
18POS TERMI-BLOK PCB MOUNT



TE Part #5-1609987-8  
CORCOM SRB SERIES IEC FILTERED  
INLETS



TE Part #1-1423673-8  
W51-A151A1-15=CKTBKR,THERM,  
ROC



TE Part #1-1579004-2  
CSV10 CRIMPING HANDTOOL  
SOLARLOK 4-6



TE Part #1954381-2  
Asy,Grounding Clip,10-12 AWG w



TE Part #1622293-1  
LR0204 1% 91R

## Documents

### CAD Files

Customer View Model

[ENG\\_CVM\\_1740277-2\\_D1.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1740277-2\\_D1.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1740277-2\\_D1.2d\\_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[CONNECTIVITY\\_SYSTEMS\\_FOR\\_PV\\_INSTALLERS\\_3-1773458-6](#)

English

[SOLARLOK\\_CONNECTIVITY\\_SYSTEMS\\_FOR\\_PV\\_MANUFACTURERS\\_3-1773458-7](#)

English

### Agency Approvals

UL Report

English