



TE Internal #: 2-1437720-3

Standard Circular Connectors, Cable-to-Cable, 3 Position, Sealable, Wire & Cable, 2A Contact Current Rating (Max), Signal, Reverse Gender, Nickel

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Cable**

Number of Positions: **3**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **2 A**

Features

Product Type Features

Product Type	Connector
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle
Shell Type	Plastic

Configuration Features

Number of Positions	3
Number of Power Positions	0
Number of Signal Positions	3
Contacts Preloaded	Yes

Body Features

Shell Plating Material	Nickel
Shell Base Material	Zinc Die Cast
Circular Connector Insulation Material Type	Polyamide

Contact Features

Contact Current Rating (Max)	2 A
Reverse Gender	Yes
Contact Layout Arrangement	Circular



Circular Connector Contact Type	Socket
---------------------------------	--------

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Retention	With

Usage Conditions

Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
Shielded	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts



TE Part # 1-1437720-3
T01-0590-PS03=T01-0590-PS03

Customers Also Bought



TE Part #1622820-2
SMD Power Resistor: 1 Watt, 3520 Series



TE Part #1-1437719-5
T01-0550-P03-MALE PLUG CONNECTOR SOLDER



TE Part #1437719-8
T01-0500-S=INDUSTRIAL CONNECTO



TE Part #160292
PLASTI-GRIP, RING, 12-10 M5




TE Part #1879222-9
CPF 0603 23R2 0.1% 25PPM 1K RL



TE Part #1-329631-2
JAM NUT, PLATED



TE Part #CQ50633001
LWB-103-6.0(10)



TE Part #1624024-1
SC30-10-2520-10 3.9UH AMMO 1000



TE Part #1437719-5
T01-0500-P=INDUSTRIAL CONNECTO



TE Part #1SNA115663R2300
M4/8.SFD

Documents

Product Drawings

T01-0599-B03-B=INDUSTRIAL CONN

English

Product Specifications

Product Specification

English

