



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [NECTOR M Series](#)



Circular Connector Hardware(1)



Plug & Socket Lighting Connector Accessories(1)



Rectangular Connector Hardware(13)



Rectangular Power Connectors(3)



Standard Circular Connectors(127)

Customers Also Bought



TE Part #1622911-1
CRG0603 1% 300K



TE Part #1622990-1
CRG0603 1% 6K2



TE Part #1623714-7
FCB4 15R 5% HP



TE Part #2213229-1
NECTOR M RING NUT, 5/6/7P, 11-14MM



TE Part #2213464-1
NECTOR M 3P PIN HSG, PNL MNT, CODE A



TE Part #2213466-1
NECTOR M 3P SCREW NUT, PNL MNT



TE Part #2213468-1
NECTOR M 3P SKT HSG ASSY, PM, CODE A



TE Part #2213263-1
NECTOR M SKT HSG ASSY, PM, 7P CODE A



TE Part #8Q526Y-000
ALR-SC-10ANSI



TE Part #1676671-1
RN 0805 23R2 0.1% 10PPM CUT LENGTH

Documents



Product Drawings

NECTOR M 3P FH PIN HOUSING, CODE F

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2213414-6_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2213414-6_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2213414-6_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773465-6_NECTOR_M

English

Agency Approvals

UL Report

English